

**N.G.O. di Reggio Calabria - Lista cavi
ALTA INTEGRAZIONE**

	CHK	Descrizione Linea	Modello Cavo	Partenza	Destinazione	Mt.
1	<input type="checkbox"/>	0-10V - Surgical Lamp 1	Percon - FTP FLEX CAT5 300MHZ	Rack	Boom arms CX	20,60
2	<input type="checkbox"/>	0-10V - Surgical Lamp 2	Percon - FTP FLEX CAT5 300MHZ	Rack	Boom arms CX	20,60
3	<input type="checkbox"/>	Spare 1 - W22	Percon - FTP FLEX CAT5 300MHZ	Rack	Boom arms CX	20,60
4	<input type="checkbox"/>	Spare 2 - W22	Percon - FTP FLEX CAT5 300MHZ	Rack	Boom arms CX	20,60
5	<input type="checkbox"/>	Button - Stop 1 - Or Table Out	Belden - 8442	Rack	Boom arms DX	19,10
6	<input type="checkbox"/>	Spare 1 - W28	Belden - 8442	Rack	Boom arms DX	19,10
7	<input type="checkbox"/>	Spare 2 - W28	Belden - 8442	Rack	Boom arms DX	19,10
8	<input type="checkbox"/>	RS232 - Touchscreen Area Sterile	Percon - FTP FLEX CAT5 300MHZ	Rack	Boom arms DX	19,10
9	<input type="checkbox"/>	TP - Extender Vga In - Touchscreen area sterile	Percon - FTP FLEX CAT5 300MHZ	Rack	Boom arms DX	19,10
10	<input type="checkbox"/>	Spare 1 - W22	Percon - FTP FLEX CAT5 300MHZ	Rack	Boom arms DX	19,10
11	<input type="checkbox"/>	Spare 2 - W22	Percon - FTP FLEX CAT5 300MHZ	Rack	Boom arms DX	19,10
12	<input type="checkbox"/>	Y - Surgical Camera Out	Sommer - 600-0051L	Rack	Boom arms SX	21,80
13	<input type="checkbox"/>	C - Surgical Camera Out	Sommer - 600-0051L	Rack	Boom arms SX	21,80
14	<input type="checkbox"/>	Y - Twin Monitor 1 In	Sommer - 600-0051L	Rack	Boom arms SX	21,80
15	<input type="checkbox"/>	C - Twin Monitor 1 In	Sommer - 600-0051L	Rack	Boom arms SX	21,80
16	<input type="checkbox"/>	Y - Single Screen In	Sommer - 600-0051L	Rack	Boom arms SX	21,80
17	<input type="checkbox"/>	C - Single Screen In	Sommer - 600-0051L	Rack	Boom arms SX	21,80
18	<input type="checkbox"/>	SDI - Single Screen In	Sommer - 600-0051L	Rack	Boom arms SX	21,80
19	<input type="checkbox"/>	SDI - Twin Monitor 1 In	Sommer - 600-0051L	Rack	Boom arms SX	21,80
20	<input type="checkbox"/>	Spare 1 - W25	Sommer - 600-0051L	Rack	Boom arms SX	21,80
21	<input type="checkbox"/>	Spare 2 - W25	Sommer - 600-0051L	Rack	Boom arms SX	21,80
22	<input type="checkbox"/>	RS232 - Surgical Camera	Percon - FTP FLEX CAT5 300MHZ	Rack	Boom arms SX	21,80
23	<input type="checkbox"/>	Spare 1 - W22	Percon - FTP FLEX CAT5 300MHZ	Rack	Boom arms SX	21,80
24	<input type="checkbox"/>	Spare 2 - W22	Percon - FTP FLEX CAT5 300MHZ	Rack	Boom arms SX	21,80
25	<input type="checkbox"/>	Y - II Out	Sommer - 600-0051L	Rack	Medical Tower	20,60
26	<input type="checkbox"/>	C -II Out	Sommer - 600-0051L	Rack	Medical Tower	20,60
27	<input type="checkbox"/>	Y - Dvd Recorder Out	Sommer - 600-0051L	Rack	Medical Tower	20,60
28	<input type="checkbox"/>	C - Dvd Recorder Out	Sommer - 600-0051L	Rack	Medical Tower	20,60
29	<input type="checkbox"/>	Y - 2 In	Sommer - 600-0051L	Rack	Medical Tower	20,60
30	<input type="checkbox"/>	C - 2 In	Sommer - 600-0051L	Rack	Medical Tower	20,60
31	<input type="checkbox"/>	Y - Dvd recorder In	Sommer - 600-0051L	Rack	Medical Tower	20,60
32	<input type="checkbox"/>	C - Dvd recorder In	Sommer - 600-0051L	Rack	Medical Tower	20,60
33	<input type="checkbox"/>	II Out	Sommer - 600-0051L	Rack	Medical Tower	20,60
34	<input type="checkbox"/>	Spare 1 - W25	Sommer - 600-0051L	Rack	Medical Tower	20,60
35	<input type="checkbox"/>	Spare 2 - W25	Sommer - 600-0051L	Rack	Medical Tower	20,60

**N.G.O. di Reggio Calabria - Lista cavi
ALTA INTEGRAZIONE**

	CHK	Descrizione Linea	Modello Cavo	Partenza	Destinazione	Mt.
36	<input type="checkbox"/>	RS232 - Dvd Recorder	Percon - FTP FLEX CAT5 300MHZ	Rack	Medical Tower	20,60
37	<input type="checkbox"/>	TP - IR Trasmitter	Percon - FTP FLEX CAT5 300MHZ	Rack	Medical Tower	20,60
38	<input type="checkbox"/>	RS232 - Medical Interface	Percon - FTP FLEX CAT5 300MHZ	Rack	Medical Tower	20,60
39	<input type="checkbox"/>	RS232	Percon - FTP FLEX CAT5 300MHZ	Rack	Medical Tower	20,60
40	<input type="checkbox"/>	TP - Extender Vga Out	Percon - FTP FLEX CAT5 300MHZ	Rack	Medical Tower	20,60
41	<input type="checkbox"/>	Spare 1 - W22	Percon - FTP FLEX CAT5 300MHZ	Rack	Medical Tower	20,60
42	<input type="checkbox"/>	Spare 2 - W22	Percon - FTP FLEX CAT5 300MHZ	Rack	Medical Tower	20,60
43	<input type="checkbox"/>	Endobase Remote	Sommer - 200-0401	Rack	Medical Tower	20,60
44	<input type="checkbox"/>	AUDIO - Dvd Recorder In	Sommer - 200-0401	Rack	Medical Tower	20,60
45	<input type="checkbox"/>	AUDIO - Dvd Recorder Out	Sommer - 200-0401	Rack	Medical Tower	20,60
46	<input type="checkbox"/>	AUDIO - 2 In	Sommer - 200-0401	Rack	Medical Tower	20,60
47	<input type="checkbox"/>	Spare 1 - W23	Sommer - 200-0401	Rack	Medical Tower	20,60
48	<input type="checkbox"/>	Spare 2 - W23	Sommer - 200-0401	Rack	Medical Tower	20,60
49	<input type="checkbox"/>	Y - TFT 40" In	Sommer - 600-0051L	Rack	Plasma panel - TFT	19,50
50	<input type="checkbox"/>	C - TFT 40" In	Sommer - 600-0051L	Rack	Plasma panel - TFT	19,50
51	<input type="checkbox"/>	SDI - Converter HSDSI/HDMI In	Sommer - 600-0051L	Rack	Plasma panel - TFT	19,50
52	<input type="checkbox"/>	Spare 1 - W25	Sommer - 600-0051L	Rack	Plasma panel - TFT	19,50
53	<input type="checkbox"/>	Spare 2 - W25	Sommer - 600-0051L	Rack	Plasma panel - TFT	19,50
54	<input type="checkbox"/>	Trasporto CAT5	Percon - FTP FLEX CAT5 300MHZ	Rack	Plasma panel - TFT	19,50
55	<input type="checkbox"/>	Trasporto CAT5	Percon - FTP FLEX CAT5 300MHZ	Rack	Plasma panel - TFT	19,50
56	<input type="checkbox"/>	Spare 1 - W22	Percon - FTP FLEX CAT5 300MHZ	Rack	Plasma panel - TFT	19,50
57	<input type="checkbox"/>	Spare 2 - W22	Percon - FTP FLEX CAT5 300MHZ	Rack	Plasma panel - TFT	19,50
58	<input type="checkbox"/>	SPK - Speaker 1	Sommer - MERIDIAN SP240	Rack	Speaker	19,10
59	<input type="checkbox"/>	SPK - Speaker 2	Sommer - MERIDIAN SP240	Rack	Speaker	18,00
60	<input type="checkbox"/>	SPK - Speaker 3	Sommer - MERIDIAN SP240	Rack	Speaker	17,80
61	<input type="checkbox"/>	SPK - Speaker 4	Sommer - MERIDIAN SP240	Rack	Speaker	14,50
62	<input type="checkbox"/>	Spare 1 - W24	Sommer - MERIDIAN SP240	Rack	Speaker	19,10
63	<input type="checkbox"/>	Spare 2 - W24	Sommer - MERIDIAN SP240	Rack	Speaker	18,00
64	<input type="checkbox"/>	Button - Stop 2 - Or Table Out	Belden - 8442	Rack	Technical panel Touchscreen	22,80
65	<input type="checkbox"/>	Button - Stop 2 - Or Table In	Belden - 8442	Rack	Technical panel Touchscreen	22,80
66	<input type="checkbox"/>	Spare 1 - W28	Belden - 8442	Rack	Technical panel Touchscreen	22,80
67	<input type="checkbox"/>	Spare 2 - W28	Belden - 8442	Rack	Technical panel Touchscreen	22,80
68	<input type="checkbox"/>	RS232 - Touchscreen Panel	Percon - FTP FLEX CAT5 300MHZ	Rack	Technical panel Touchscreen	22,80
69	<input type="checkbox"/>	TP - Extender Mouse-keyb In	Percon - FTP FLEX CAT5 300MHZ	Rack	Technical panel Touchscreen	22,80
70	<input type="checkbox"/>	TP - Extender Vga In - Touchscreen Panel	Percon - FTP FLEX CAT5 300MHZ	Rack	Technical panel Touchscreen	22,80
71	<input type="checkbox"/>	Spare 1 - W22	Percon - FTP FLEX CAT5 300MHZ	Rack	Technical panel Touchscreen	22,80
72	<input type="checkbox"/>	Spare 2 - W22	Percon - FTP FLEX CAT5 300MHZ	Rack	Technical panel Touchscreen	22,80

**N.G.O. di Reggio Calabria - Lista cavi
ALTA INTEGRAZIONE**

	CHK	Descrizione Linea	Modello Cavo	Partenza	Destinazione	Mt.
73	<input type="checkbox"/>	CV - Patch Panel	Sommer - 600-0051L	Rack	Technical panel Touchscreen	22,80
74	<input type="checkbox"/>	CV - Patch Panel (Option)	Sommer - 600-0051L	Rack	Technical panel Touchscreen	22,80
75	<input type="checkbox"/>	SDI - Patch Panel OUT	Sommer - 600-0051L	Rack	Technical panel Touchscreen	22,80
76	<input type="checkbox"/>	Spare 1 - W25	Sommer - 600-0051L	Rack	Technical panel Touchscreen	22,80
77	<input type="checkbox"/>	Spare 2 - W25	Sommer - 600-0051L	Rack	Technical panel Touchscreen	22,80
78	<input type="checkbox"/>	AUDIO - Patch Panel Out	Sommer - 200-0401	Rack	Technical panel Touchscreen	22,80
79	<input type="checkbox"/>	AUDIO - Patch Panel In	Sommer - 200-0401	Rack	Technical panel Touchscreen	22,80
80	<input type="checkbox"/>	AUDIO - Patch Panel Out (Option)	Sommer - 200-0401	Rack	Technical panel Touchscreen	22,80
81	<input type="checkbox"/>	Spare 1 - W23	Sommer - 200-0401	Rack	Technical panel Touchscreen	22,80
82	<input type="checkbox"/>	Spare 2 - W23	Sommer - 200-0401	Rack	Technical panel Touchscreen	22,80
83	<input type="checkbox"/>	Y - Videoconference Camera	Sommer - 600-0051L	Rack	Videoconf	19,50
84	<input type="checkbox"/>	C - Videoconference Camera	Sommer - 600-0051L	Rack	Videoconf	19,50
85	<input type="checkbox"/>	Spare 1 - W25	Sommer - 600-0051L	Rack	Videoconf	19,50
86	<input type="checkbox"/>	Spare 2 - W25	Sommer - 600-0051L	Rack	Videoconf	19,50
87	<input type="checkbox"/>	RF - Antenna 1	Sommer - SC-CLASSIC MKII	Rack	Videoconf	19,50
88	<input type="checkbox"/>	RF - Antenna 2	Sommer - SC-CLASSIC MKII	Rack	Videoconf	19,50
89	<input type="checkbox"/>	Spare 1 - W50	Sommer - SC-CLASSIC MKII	Rack	Videoconf	19,50
90	<input type="checkbox"/>	Spare 2 - W50	Sommer - SC-CLASSIC MKII	Rack	Videoconf	19,50
91	<input type="checkbox"/>	RS232 - Videoconference Camera	Percon - FTP FLEX CAT5 300MHZ	Rack	Videoconf	19,50
92	<input type="checkbox"/>	Spare 1 - W22	Percon - FTP FLEX CAT5 300MHZ	Rack	Videoconf	19,50
93	<input type="checkbox"/>	Spare 2 - W22	Percon - FTP FLEX CAT5 300MHZ	Rack	Videoconf	19,50
94	<input type="checkbox"/>	TP - Extender Vga In - Universal Display	Percon - FTP FLEX CAT5 300MHZ	Medical Tower	Boom arms DX	20,30
95	<input type="checkbox"/>	Spare 1 - W22	Percon - FTP FLEX CAT5 300MHZ	Medical Tower	Boom arms DX	20,30
96	<input type="checkbox"/>	Spare 2 - W22	Percon - FTP FLEX CAT5 300MHZ	Medical Tower	Boom arms DX	20,30
97	<input type="checkbox"/>	OUT --- Twin Screen In	Sommer - 600-0051L	Medical Tower	Boom arms SX	20,30
98	<input type="checkbox"/>	OUT --- Twin Screen In	Sommer - 600-0051L	Medical Tower	Boom arms SX	20,30
99	<input type="checkbox"/>	Spare 1 - W25	Sommer - 600-0051L	Medical Tower	Boom arms SX	20,30
100	<input type="checkbox"/>	Spare 2 - W25	Sommer - 600-0051L	Medical Tower	Boom arms SX	20,30